



CareFit™ Combo Extender

MOUNTING OPTIONS


The CareFit™ Combo **Extender** accessory can only be added to an Arm mounted to Wood Stud, Metal Stud, or Solid Concrete. The Extender **CAN NOT** be added to an Arm mounted to **Hollow Wall**.




RANGE OF MOTION



DIMENSIONS



Pushed back against the wall



Download additional resources at ergotron.com

USA & Canada Sales & Corporate Headquarters: St. Paul, MN USA / 800.888.8458 / +1.651.681.7600 / insidesales@ergotron.com

EMEA Sales: Amersfoort, The Netherlands / +31.33.45.45.600 / info.eu@ergotron.com

APAC Sales: Sydney, Australia / apaccustomerservice@ergotron.com

LATAM Sales: Mexico / +1.800.681.1820 / info.latam@ergotron.com


Worldwide Custom Sales: custom@ergotron.com

Ergotron devices are not intended to cure, treat, mitigate or prevent any disease. Patent information available at www.ergotron.com/patents


© 2022 Ergotron, Inc. rev. 05/11/2022 DIM-CFArmExt Content is subject to change without notification

CareFit™ Combo Extender

DIMENSIONS




Arm Full UP




Side View

Arm Full DOWN




Side View

Fully Extended



Side View

Folded Up Against Wall





Side View


CareFit™ Combo Extender

CABLES


Cable length needed based on equipment and accessories:



- Cables:**
HDMI: 8' (2.4 m)
Ethernet: 8' - 12' (2.4-3.7 m)
Monitor Power: 8' - 12' (2.4-3.7 m)
2.0 USB Extenders: 8' (2.4 m) per accessory



- Cables:**
HDMI: 4' (1.2 m)
Ethernet: 8' - 12' (2.4-3.7 m)
Monitor Power: 8' - 12' (2.4-3.7 m)
Computer Power: 8' - 12' (2.4-3.7 m)



- Cables:**
Ethernet: 8' - 12' (2.4-3.7 m)
Monitor Power: 8' - 12' (2.4-3.7 m)